

Ultrx WiFi Window Door Type 4X, 608x595x321mm, Lt Gray, Fiberglass

CATALOG NUMBER

DU606030WP



Ideal for locations such as tunnels, floor vaults, marinas, outside walls or rooftops, the lightweight Ultrx fiberglass WiFi cabinet does not impede WiFi or WLAN signals and has optional rack angles that can be added to support 19-inch rack-mount equipment.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12, 13; File No. E61997

Enclosure flammability rating per UL 508

Window flammability rating per UL 508

NEMA/EEMAC Type 4, 4X, 12, 13

IEC 60529, IP66

Cabinets with solid doors are plenum rated.

FEATURES

Fiberglass is easily punched, drilled, filed or sawed

Seamless foam-in-place gasket assures watertight and dusttight seal

Enclosure may be rotated 180 degrees for left and right hinging

Molded-in drip shields are standard with each enclosure

Door opens 180 degrees

Replaceable breakaway hinges

Keylocking handle standard

Molded-in DIN bosses

Molded bosses on door provide additional mounting provisions

Integral mounting rails provide infinite panel adjustment front to back

Optional data pocket is high-impact thermoplastic

Enclosure and door made of molded fiberglass polyester that resists chemicals and temperature change

Impact-resistant polycarbonate window is permanently bonded in place

Fiberglass mounting brackets and stainless steel attachment screws are provided with each enclosure

Includes a 3/4-inch plywood panel for mounting equipment

PRODUCT ATTRIBUTES

Article Number: 14958

Height: 23.94in

Width: 23.43in

Depth: 12.64in

Material: Fiberglass

Finish: Smooth Matte

Color: Light Gray

Color Code: RAL 7035

Thickness: 0.15in

Window Size: 19.62 x 19.12in

Mounting: 21.86 x 22.36in

Door Type: Window

Internal Dimensions: 23.94 x 23.44 x 12.64in

Weight: 43lb

ADDITIONAL PRODUCT DETAILS

Wood panel included with enclosure, optional steel panels must be ordered separately

Window size applies to window door cabinets only

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE