

Sloped-Front Pushbutton Square Enclosures Type 12, 16PBx30.5mm, Gray, Steel

CATALOG NUMBER

E16PBA



These Sloped Front Pushbutton Enclosures are designed to hold 30.5-mm or 22.5-mm pushbuttons and switches where slanted control surfaces are desired.

INDUSTRY STANDARDS

UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12, 13

IEC 60529, IP65

FEATURES

Seams continuously welded and ground smooth

Captivated cover screws thread into sealed wells

Grounding stud on body

Bonding provision on cover

Oil-resistant gasket

Factory stamped 4-way pushbutton holes

Enclosures 7.25 x 6.25 x 6.75 in. (184 x 159 x 171 mm) and larger have internal detachable hinge to hold cover open during wiring, yet permit immediate removal

External welded-on mounting brackets for easy installation

30.5-mm or 22.5-mm size holes

PRODUCT ATTRIBUTES

Article Number: 58620

Height: 11.75in

Width: 10.75in

Depth: 9in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Hole Size: 1.2in

Hole Quantity: 16

Mounting: 11.19 x 9.88in

Overall Dimensions: 11.69 x 10.97in

Weight: 12.4lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE