

Extra-Deep Pushbutton Screw Cover Type 4X, 16PBx30.5mm, SS304

CATALOG NUMBER

E16PBXSS



Designed to house 30.5-mm oil-tight pushbuttons, switches and pilot lights. Enclosures provide protection against dirt, dust, oil and water. Extra-deep design accommodates additional contact blocks for pushbuttons. See Mild Steel chapter for related mild steel enclosures.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File Number E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File Number E61997

NEMA/EEMAC Type 4X, 12, 13

IEC 60529, IP66

FEATURES

Extra-deep design accommodates additional contact blocks for pushbuttons.

Seams continuously welded and ground smooth

Captivated cover screws thread into sealed wells

Bonding provision on door; grounding nut on body

4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights

Enclosures 6.00 x 4.00 x 4.75 in. (152 x 102 x 121 mm) and larger have internal detachable hinge to hold cover open during wiring, yet permit immediate removal

Oil-resistant gasket

PRODUCT ATTRIBUTES

Article Number: 59600

Height: 11.75in

Width: 10.75in

Depth: 4.75in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 14ga

Hole Quantity: 16

Overall Dimensions: 12.75 x 10.97in

Mounting: 12.25 x 9.88in

Weight: 9.9lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte