

Side-Mount Cabinet 19-inch 2U, Black, Steel

CATALOG NUMBER

E19SM2U



Equipment mounts sideways against the wall; ideal for applications where a low profile is required. Easily removable front cover protects equipment. Integral Velcro® cable tiedown slots facilitate cable routing. Shipped fully assembled. Velcro is a trademark of Velcro Industries B.V.

INDUSTRY STANDARDS

UL 2416 Listed; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

FEATURES

Equipment mounts sideways against the wall; ideal for applications where a low profile is required

Easily removable front cover protects equipment. Integral Velcro® cable tiedown slots facilitate cable routing

Shipped fully assembled

PRODUCT ATTRIBUTES

Article Number: 11022

Height: 20in

Width: 16.5in

Depth: 3.5in

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 16ga

Rack Units: 2U

Load Rating: 50lb

Weight: 15.1lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE