

Extra-Deep Pushbutton Screw Cover Type 4X, 1PBx22.5mm, SS304

CATALOG NUMBER

E1PBGXSS



Designed to house 22.5-mm oil-tight pushbuttons, switches and pilot lights. Enclosures provide protection against dust, dirt, oil and water. Extra-deep design accommodates additional contact blocks for pushbuttons.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File Number E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File Number E61997

NEMA/EEMAC Type 4X, 12, 13

IEC 60529, IP66

FEATURES

Extra-deep design accommodates additional contact blocks for pushbuttons.

Seams continuously welded and ground smooth

Captivated stainless steel cover screws thread into sealed wells

Enclosures 8.50 x 4.00 x 4.75 in. (216 x 102 x 121 mm) and larger have internal detachable hinge to hold cover open during wiring, yet permit immediate removal

Bonding provision on door; grounding nut on body

Oil-resistant gasket

PRODUCT ATTRIBUTES

Article Number: 60230

Height: 4in

Width: 4in

Depth: 4.75in

Material: Stainless Steel 304

Finish: Brushed #4

Body Thickness: 16ga

Door Thickness: 16ga

Overall Dimensions: 5.00 x 4.22in

Mounting: 4.50 x 3.13in

Hole Quantity: 1

Weight: 2.5lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE