

Pushbutton Enclosures Type 12, 8PBx30.5mm, Gray, Steel

CATALOG NUMBER

E8PB



These pushbutton enclosures are designed to hold 30.5-mm or 22.5-mm pushbuttons and switches.

INDUSTRY STANDARDS

UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12, 13

IEC 60529, IP65

FEATURES

Seams continuously welded and ground smooth

Captivated cover screws thread into sealed wells

Bonding provision on cover

Grounding stud on body

Oil-resistant gasket

Factory stamped 4-way pushbutton holes

Enclosures with more than one column of pushbutton holes have internal detachable hinge to hold cover open during wiring

External welded-on mounting brackets for easy installation

30.5-mm or 22.5-mm size holes

PRODUCT ATTRIBUTES

Article Number: 57840

Height: 20.25in

Width: 3.25in

Depth: 2.75in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Hole Size: 1.2in

Hole Quantity: 8

Overall Dimensions: 21.25 x 3.47in

Mounting: 20.75 x 2.38in

Weight: 5.9lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE