

Deep Pushbutton Enclosures Type 12, 9PB x 22.5mm, Gray, Steel

CATALOG NUMBER

E9PBGXM



Designed for pushbuttons and switches, the extra depth of these enclosures accommodates additional pushbutton contact blocks.

INDUSTRY STANDARDS

UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12, 13

IEC 60529, IP65

FEATURES

Seams continuously welded and ground smooth

Captivated cover screws thread into sealed wells

Bonding provision on cover

Grounding nut in body of enclosure

Oil-resistant gasket

Enclosures with more than one column of pushbutton holes have internal detachable hinge to hold cover open during installation

External welded-on mounting brackets for easy installation

Factory stamped 4-way pushbutton holes

22.5-mm size holes

PRODUCT ATTRIBUTES

Article Number: 13533

Height: 8.5in

Width: 7.25in

Depth: 4.25in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Hole Quantity: 9

Mounting: 9.00 x 5.63in

Overall Dimensions: 9.50 x 7.47in

Weight: 6.4lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE