

ComLine Enclosure Hidden Hinge Type 4X, 1200x900x300mm, Gray, Aluminum

CATALOG NUMBER

ECL1209030



Lightweight, corrosion-resistant ComLine aluminum wall-mount enclosures provide long-lasting protection for housing electrical components in extreme outdoor environments. These customizable enclosures employ a foam-in-place gasket for a tight seal and are ideal for rooftop or tower-mounted telecommunications applications.

INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12; File No. E61997

CSA File No. 42186: Type 3, 3R, 4, 4X, 12

NEMA/EEMAC Type 3, 3R, 4, 4X, 12

IEC 60529, IP66

Designed to meet NEBS™-Telcordia GR487, GR63, IEC 48D

Meets Type 3RX requirements

NEBS is a trademark of Telcordia

FEATURES

Bonding provision on door; ground stud on body

Seams continuously welded and ground smooth for a finished appearance

Foam-in-place seamless gasket for superior protection against dust and liquid ingress

1- or 3-point latching (screwdriver slot), depending on door size

Optional door stop/wind latch holds door in place during service

Two door/hinge styles available

Easily removable door with hidden hinge and retaining hinge pin

PRODUCT ATTRIBUTES

Article Number: 37159

Height (H): 47.24in

Width (W): 35.43in

Depth (D): 11.81in

Material: Aluminum

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Body Thickness: 0.08in


Door Thickness: 0.1in

Latch Quantity: 3

Package Weight: 55lb

Weight: 45lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE