

Drawn Pushbutton Enclosures Type 4, 1PBx22.5mm; 5.75x4.00x3.75, Gray, Steel

CATALOG NUMBER

ED2PBM



Drawn Pushbutton Enclosures are designed to hold 30.5-mm or 22.5-mm 4-way pushbuttons and switches. These enclosures have no welded seams or sharp corners.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 4, 12, 13

IEC 60529, IP66

FEATURES

Drawn enclosure

No welded seams or sharp corners

Cover screws outside gasket sealing surface

Flat or domed flanged cover

Grounding stud on body

Bonding provision on cover

Oil-resistant gasket

External welded-on mounting brackets for easy installation

Factory stamped 4-way pushbutton holes

30.5-mm or 22.5-mm size holes

PRODUCT ATTRIBUTES

Article Number: 57760

Height: 5.75in

Width: 4in

Depth: 3.75in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Hole Size: 0.88in

Hole Quantity: 2

Mounting: 6.25 x 2.38in

Cover Style: Flat

Weight: 2.2lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE