


Open Frame Rack 2-Post, 48.00x24.25x15.00, Black, Aluminum

CATALOG NUMBER

EDR23FM24U



Designed for use in communication data centers and telecommunication rooms, 2-Post Open Frame Racks satisfy basic functional requirements for structuring cable. Racks are available in 3-inch or 6-inch column widths.

INDUSTRY STANDARDS

UL 2416 Listed; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

FEATURES

Range of heights from 4 feet to 9 feet (24U to 58U) to match capacity requirements; 19-inch Rack Packages are 7-feet high

Side rails are tapped on both sides with 12-24UNC threads for quick installation

EIA Universal 5/8 inch - 5/8 inch - 1/2 inch vertical mounting hole pattern matches industry standards

RU markings on both front and back of uprights make it easier to mount equipment

Packed unassembled in individual cartons; assembly hardware is furnished for convenient storage and installation

Convenient rack and cable manager packages offered with either one or two 6-inch cable managers; includes one-piece hinged cover

PRODUCT ATTRIBUTES

Article Number: 21649

Height: 48in

Width: 24.25in

Depth: 15in

Material: Aluminum

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 0.14in

Rack Units: 24U

Weight: 22.6lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE