


Rack Angles Square 26U, fits 48.00, Black, Steel

CATALOG NUMBER

EWMR48S



The AccessPlus Rack Angles are used to mount 19in rack equipment inside the AccessPlus product. They have EIA universal spaced, 19-in. rack-mounting holes that are RU marked from bottom to top. The rack angle holes are either 10-32 tapped or square. Please note twenty mounting screws are included.

FEATURES

The AccessPlus Rack Angles are used to mount 19in rack equipment inside the AccessPlus product

They have EIA universal spaced, 19-in. rack-mounting holes that are RU marked from bottom to top

The rack angle holes are either 10-32 tapped or square

Twenty mounting screws included

PRODUCT ATTRIBUTES

Article Number: 17896

Material: Mild Steel

Finish: Zinc Plated

Thickness: 12ga

Rack Units: 26U

Fits Cabinet: A = 48.00in

Weight: 5lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE