

Elbow 45-Degree Lay-in, 10.00x10.00, Galvanized, Steel

CATALOG NUMBER

F101045EGV



Lay-in Galvanized 45-Degree Elbows are used for continuous run with 45-degree turns. Any side can be removed, retaining lay-in feature regardless of how the elbow is oriented. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sides are held together with screws.

FEATURES

Lay-in Galvanized 45-Degree Elbows are used for continuous run with 45-degree turns

Any side can be removed, retaining lay-in feature regardless of how the elbow is oriented

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sides are held together with screws

PRODUCT ATTRIBUTES

Article Number: 45830

Type: Elbow

Height: 10in

Width: 10in

Material: Mild Steel

Finish: Galvanized

Thickness: 14ga

Weight: 7.5lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE