

Screw Cover Wiring Trough Type 12, 2.50x2.50x12.00, Gray, Steel

CATALOG NUMBER

F2212SC



Screw-Cover Wiring Trough, Type 12 is used for protecting wire and cable distribution, junctions and terminations in a variety of moist or dirty applications.

INDUSTRY STANDARDS

UL 870 Listed; File No. E27524

NEMA/EEMAC Type 12

JIC standards EGP-1-1967 and EMP-1-1967

CSA, File No. 42184: Type 12

IEC 60529, IP55

FEATURES

Ends and seams continuously welded and ground smooth; no holes or knockouts

Captivated cover screws thread into sealed wells

Oil-resistant gasket and adhesive

Wiring Troughs are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 15350

Type: Trough

Height: 2.5in

Width: 2.5in

Depth: 12in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Fastener Quantity: 4

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE