


Elbow 90-Degree Lay-in, 2.50x2.50, Galvanized, Steel

CATALOG NUMBER

F2290EGV



Lay-in Galvanized 90-Degree Elbows are used for right-angle installations. Any side can be removed, retaining lay-in feature regardless of how the elbow is oriented. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sides are held together with screws.

FEATURES

Lay-in Galvanized 90-Degree Elbows are used for right-angle installations

Any side can be removed, retaining lay-in feature regardless of how the elbow is oriented

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sides are held together with screws

PRODUCT ATTRIBUTES

Article Number: 88000

Type: Elbow

Height: 2.5in

Width: 2.5in

Material: Mild Steel

Finish: Galvanized

Thickness: 16ga

Weight: 1.14lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE