

Straight Section Lay-in Hinged-Cover Type 1 no KOs, 2.5x2.5x60, Gray, Steel

CATALOG NUMBER

F22G60



Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.

FEATURES

Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs

Sections are completely open on one side so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sections are available in lengths from 12 inch to 120 inch, with or without knockouts

PRODUCT ATTRIBUTES

Article Number: 52050

Type: Straight Section

Height: 2.5in

Width: 2.5in

Depth: 60in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Weight: 13lb

Cover Style: Hinge

ADDITIONAL PRODUCT DETAILS

F1212GXX catalog numbers without "H" are not hinged. F1212GXXH catalog numbers are hinged.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE