

Elbow 45-Degree Lay-in, 2.50x2.50, Gray, Steel

CATALOG NUMBER

F22G45E



Lay-in Painted 45-Degree Elbows are used for continuous run with 45-degree turns. Top and inside covers removable so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Painted 45-Degree Elbows are used for continuous run with 45-degree turns

Top and inside covers removable so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

PRODUCT ATTRIBUTES

Article Number: 52080

Type: Elbow

Height: 2.5in

Width: 2.5in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Weight: 0.88lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE