


Cutoff Fitting Non-Lay-in, 2.50x2.50, Gray, Steel

CATALOG NUMBER

F22LX



Non-Lay-In Hinged Cover Cutoff Fittings are used for lengths up to 12.00 inch (305 mm). Body comes in two pieces. Shorten body and cover to the desired length and weld together. Shorten body to desired length and weld on flange. This is not a "lay-in" fitting but often is used when entering an enclosure. Fittings are finished with paint over plated surfaces.

FEATURES

Non-Lay-In Hinged Cover Cutoff Fittings are used for lengths up to 12.00 inch (305 mm)

Body comes in two pieces. Shorten body and cover to the desired length and weld together

Shorten body to desired length and weld on flange

"This is not a "lay-in" fitting but often is used when entering an enclosure"

Fittings are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 18080

Type: Cut-Off Fitting

Height: 2.5in

Width: 2.5in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Sealing Plate Type: 90°

Sealing Plate Quantity: 1

Weight: 3.6lb

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE