

Straight Section Lay-in Flat-Cover Type 1 no KOs, 2.5x2.5x60, Gray, Steel

CATALOG NUMBER

F22T160GVP



Lay-in Flat-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wire and cable can be laid-in along run, which eliminates the action of pulling wires or cables that can result in insulation damage.

FEATURES

Lay-in Flat-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs

Sections are completely open on one side so wires and cables can be laid-in along run

Lay-in design eliminates the action of pulling wires or cables, which can result in insulation damage

Flat-cover design supports mounting flush with walls or ceilings

Covers feature keyhole screw slots which simplify cover installation and removal, and limit risk of losing securing screws

Sections available in lengths from 12 to 120 inches, with or without knockouts

4"x4" and 6"x6" Straight Sections re-designed with Snap Connect features for ease-of-installation; sections are backwards compatible if a legacy U-Connector is present

PRODUCT ATTRIBUTES

Article Number: 35949

Type: Straight Section

Height: 2.5in

Width: 2.5in

Depth: 60in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Weight: 11.25lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE