

Screw Cover Wiring Trough NEMA Type 4X, 4.00x4.00x18.00, Brushed, SS304

CATALOG NUMBER

F4418SCSS



Stainless Steel Screw-Cover Wiring Trough, Type 4X is used for protecting wire and cable distribution, junctions and terminations in outdoor or corrosive applications in which frequent access is not needed.

INDUSTRY STANDARDS

UL 870, 50E Listed; Type 12/3R/4/4X; File No. E27524; cUL Listed

per CSA C22.2 No. 26 and No. 94.2; Type 3R, 4, 4X, 12

IEC 60529, IP66

FEATURES

Seams continuously welded and ground smooth

Oil-resistant gasket and adhesive

Captivated stainless steel cover screw threaded into sealed walls

No holes or knockouts

PRODUCT ATTRIBUTES

Article Number: 30584

Type: Trough

Height: 4in

Width: 4in

Depth: 18in

Material: Stainless Steel 304

Finish: No. 2B

Body Thickness: 16ga

Door Thickness: 14ga

Cover Screw Quantity: 6

Weight: 7.7lb

ADDITIONAL PRODUCT DETAILS

Omit center mounting foot if C is less than 60 in. (1524 mm).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE