

# Straight Section Lay-in Hinged-Cover Type 1 with KOs, 4x4x12, Gray, Steel

## CATALOG NUMBER

**F44G12WK**



Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.

## FEATURES

Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs

Sections are completely open on one side so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sections are available in lengths from 12 inch to 120 inch, with or without knockouts

## PRODUCT ATTRIBUTES

Article Number: 52900

Type: Straight Section

Height: 4in

Width: 4in

Depth: 12in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Knockout Sizes: (4) 0.50 - 0.75"

Weight: 3.6lb

## ADDITIONAL PRODUCT DETAILS

---

F1212GXX catalog numbers without "H" are not hinged. F1212GXXH catalog numbers are hinged.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**