

Lay-In NEMA Type 3R Wireway Straight Section, 4.00x4.00x120.00, Gray, Galv Steel

CATALOG NUMBER

F44T3R120



Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs.

FEATURES

Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs

PRODUCT ATTRIBUTES

Article Number: 43529

Type: Straight Section

Height: 4in

Width: 4in

Depth: 120in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Weight: 35lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE