

U-Connector, fits 4.00x4.00, Gray, Steel

CATALOG NUMBER

F44T3RUC



Lay-in Painted Galvanized U-Connectors are used to rigidly join fittings to lay-in wireway straight sections. Top swings aside to retain the lay-in feature. One U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates or reducers.

FEATURES

Lay-in Painted Galvanized U-Connectors are used to rigidly join fittings to lay-in wireway straight sections

Top swings aside to retain the lay-in feature

One U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates or reducers

PRODUCT ATTRIBUTES

Article Number: 43549

Type: U-Connector

Height: 4in

Width: 4in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Weight: 1.14lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE