


Straight Section Feed-Through Type 12 and 3R, 4.00x4.00x36.00, Gray, Fiberglass

CATALOG NUMBER

F44W36FG



Fiberglass Feed-Through Wireway Type 12, 3R Straight Sections are used for enclosing wire and cable in wireway runs. The traditional closed-loop design has an opening on one side for easy access to wires and cables. The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications. Sections are available in lengths from 12 inch to 60 inch.

FEATURES

Fiberglass Feed-Through Wireway, Type 12, 3R Straight Sections are used for enclosing wire and cable in wireway runs

The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications

Sections are available in lengths from 12 inch to 60 inch

The traditional closed-loop design has an opening on one side for easy access to wires and cables

PRODUCT ATTRIBUTES

Article Number: 15840

Type: Straight Section

Height: 4in

Width: 4in

Depth: 36in

Material: Fiberglass

Finish: Smooth Matte

Color: Gray

Color Code: ANSI 61

Thickness: 0.12ga

Weight: 9lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE