

Straight Tube Section Feed-Through Type 4X, 4.00x4.00x60.00, Gray, Fiberglass

CATALOG NUMBER

F44W60STFG



Feed-Through Fiberglass Hinged-Cover, Type 12, 3R Straight Tube Sections are used for enclosing wire and cable in wireway runs. The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications. Tubes are available in lengths from 12 inch to 120 inch.

FEATURES

Feed-Through Fiberglass Hinged-Cover, Type 12, 3R Straight Tube Sections are used for enclosing wire and cable in wireway runs

The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications

Tubes are available in lengths from 12 inch to 120 inch

PRODUCT ATTRIBUTES

Article Number: 19140

Type: Straight Section

Height: 4in

Width: 4in

Depth: 60in

Material: Fiberglass

Finish: Smooth Matte

Color: Gray

Color Code: ANSI 61

Thickness: 0.12ga

Weight: 10.88lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE