

Straight Section Feed-Through Type 4X, 4.00x4.00x60.00, Brushed, SS304

CATALOG NUMBER

F44W60SS



Feed-Through Stainless Steel Hinged-Cover, Type 4X Straight Sections are used for enclosing wire and cable in wireway runs. Its water-proof and stainless steel features makes it suitable for frequently hosed down, very wet or highly corrosive applications. The traditional closed-loop design has an opening on one side for easy access to wires and cables. Sections are available in lengths from 12 inch to 120 inch.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

CERTIFICATIONS



FEATURES

Feed-Through Stainless Steel Hinged-Cover, Type 4X Straight Sections are used for enclosing wire and cable in wireway runs

Its water-proof and stainless steel features makes it suitable for frequently hosed down, very wet or highly corrosive applications

The traditional closed-loop design has an opening on one side for easy access to wires and cables

Sections are available in lengths from 12 inch to 120 inch

For modification and customization, Type 316 stainless steel covers and bodies available upon request

PRODUCT ATTRIBUTES

Article Number: 15440

Type: Straight Section

Height: 4in

Width: 4in

Depth: 60in

Material: Stainless Steel 304

Finish: No. 2B

Thickness: 16ga

Weight: 22lb

ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE