

Elbow 22.50-Degree Feed-Through, 4.00x4.00, Gray, Steel

CATALOG NUMBER

F44WE225



Feed-Through 22.50-Degree Elbows are used for continuous runs with 22.50-degree turns. Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Feed-Through 22.50-Degree Elbows are used for continuous runs with 22.50-degree turns

Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications

PRODUCT ATTRIBUTES

Article Number: 15750

Type: Elbow

Height: 4in

Width: 4in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Weight: 2.5lb

ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE