

EconoTrough NEMA Type 3R, 6.00x6.00x18.00, Galvanized, Steel

CATALOG NUMBER

F6618RTGV



EconoTrough Galvanized Wiring Trough is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security.

INDUSTRY STANDARDS

UL 870 Listed; File No. E27524; Raintight

cUL CSA C22.2 No. 26 Listed; File No. E27524; Raintight

NEMA/EEMAC Type 3R

IEC 60529, IP 32

FEATURES

Removable cover

Drip-shield top covers sides, front and back

Padlock Hasp Kit available

No gasketing or knockouts

Provision for utility seal

Embossed mounting holes on back of enclosure

PRODUCT ATTRIBUTES

Article Number: 14773

Type: Trough

Height: 6in

Width: 6in

Depth: 18in

Material: Mild Steel

Finish: Galvanized

Thickness: 16ga

Weight: 11lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE