

Wiring Trough NEMA Type 12 and 3R, 6.00x6.00x60.00, Gray, Fiberglass

CATALOG NUMBER

F6660FG



Fiberglass Wiring Trough NEMA Type 12 and 3R is used for protecting wire and cable distribution, junctions and terminations. This lightweight, temperature- and chemically-resistant fiberglass trough is designed for use in corrosive or dirty indoor or outdoor applications.

INDUSTRY STANDARDS

Flammability Rating UL 94-5V

Meets UL cold impact test for temperatures to -35 C

NEMA Type 12 and Type 3R

IEC 60529, IP55

Recognized by National Electric Code for indoor and outdoor applications

FEATURES

Captivated Monel cover screws

Seams are sealed

Oil-resistant gasket attached with oil-resistant adhesive

No holes or knockouts

Pultruded fiberglass polyester bodies and covers

PRODUCT ATTRIBUTES

Article Number: 15990

Type: Trough

Height: 6in

Width: 6in

Depth: 60in

Material: Fiberglass

Finish: Smooth Matte

Color: Gray

Color Code: ANSI 61

Thickness: 0.12in

Opening Quantity: 5

Cover Screw Quantity: 14

Weight: 18lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE