

Straight Section Feed-Through Type 12, 8.00x8.00x60.00, Gray, Steel

CATALOG NUMBER

F88W60



Feed-Through Hinged-Cover, Type 12 Straight Sections are used for enclosing wire and cable in wireway runs. Its dust protection features makes it suitable for a broad range of industrial applications. The traditional closed-loop design has an opening on one side for easy access to wires and cables. Sections are available in lengths from 12 inch to 120 inch

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Feed-Through Hinged-Cover, Type 12 Straight Sections are used for enclosing wire and cable in wireway runs

Its dust protection features makes it suitable for a broad range of industrial applications

The traditional closed-loop design has an opening on one side for easy access to wires and cables

Sections are available in lengths from 12 inch to 120 inch

PRODUCT ATTRIBUTES

Article Number: 14660

Type: Straight Section

Height: 8in

Width: 8in

Depth: 60in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Weight: 48lb

ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE