

Fusion G7 Type 4 and 12, 600x500X200, Lt Gray, Steel

CATALOG NUMBER

G600500200G



Innovative, metric-dimensioned wall-mount enclosure designed to house and protect electrical and electronic components in industrial environments. Provides traditional enclosure functionality with scalable internal component mounting capability using the optional internal mounting system and accessory components.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. 61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. 61997

Wall-mounting brackets required to maintain UL/CSA external mounting requirement.

NEMA/EEMAC Type 4, 12, 13

CSA File No. 42186: Type 4, 12

IEC 60529, IP66

FEATURES

Seamless foam-in-place gasket

Reversible door with sealed hinges and hinge brackets

Gland plate(s) for enclosure bottom

Bonding provision on door; grounding studs (2) on body

Full-height galvanized steel back panel included

External formed 90-degree body flange channels away liquids

Three-point latching on enclosures 1000-mm high and taller

Door alignment device on doors with 3-point latching and 800 mm or wider

Pre-cut gland plate opening(s) in enclosure bottom

Quarter-turn latch(es) with 3-mm double-bit insert

Corner-formed door

Simple, easy-to-remove and install hinge pins with captivation clip

High-torque threadless studs and fasteners on door

Wide assortment of user-friendly internal accessories to increase internal mounting area capability and design flexibility

Hardware kit includes grounding and sealing hardware

Hinged on right side

Installation instruction provided

PRODUCT ATTRIBUTES

Article Number: 18988

Height: 23.62in

Width: 19.69in

Depth: 7.87in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Body Thickness: 18ga

Door Thickness: 16ga

Latch Type: Quarter-Turn

Weight: 35lb

ADDITIONAL PRODUCT DETAILS

NOTE: G400300150 does not have a gland plate.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE