

Fusion G7 Gland Plate, Cutout Size 90x280, Steel

CATALOG NUMBER

GGP90280



Designed for use with Fusion G7 enclosures. Provides a removable cable egress and entry plate while maintaining IP/UL/CSA integrity of the enclosure.

FEATURES

Foam-in-place gasket, fasteners and instructions provided

PRODUCT ATTRIBUTES

Article Number: 18288

Height: 13.98in

Width: 6.5in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Cutout Size: 3.54 x 11.02in

Weight: 1.6lb

ADDITIONAL PRODUCT DETAILS

Maintains IP66/UL/CSA Type 4 and 12 when properly installed on a nVent HOFFMAN enclosure.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE