

# HG Filter Fan Exhaust Grille IP55, fits HF09 fans 9-inch, Black, Plastic

## CATALOG NUMBER

**HG0900503**



HG Filter Fan Exhaust Grilles have a unique click-fit design which quickly install into enclosure wall; no tools or fasteners required. Grilles open with the flick of a finger and remains attached after opening for easy access to the filter.

## INDUSTRY STANDARDS

UL/cUL Listed; File No. E482010

CE

EAC

Type 12, IP54 standard (on all models except HF13)

Type 12, IP 55 optional (on all models except HF04)

## FEATURES

Click-Fit design quickly installs into enclosure wall; no tools or screws required

Opens with the flick of a finger for easy filter replacement

Enclosure side wall mounting

Standard rope gasket provides proper seal to the enclosure

Similar cut-out sizes as other filter fan manufacturers

Hinged grille remains attached after opening

Size range from 4 inch (102 mm) to 13 inch (325 mm)

Free air flow from 21 CFM (36 m3/hr.) to 484 CFM (822 m3/hr.)

## PRODUCT ATTRIBUTES

Article Number: 34328

Height: 8.19in

Width: 8.21in

Depth: 1.65in

Material: Plastic

Finish: Smooth Matte

Color: Graphite Black

Color Code: RAL 9011

Weight: 0.7lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**