

Filter Fan Shroud Type 3R HH10, 15.00x12.00x3.81, Brushed, SS304

CATALOG NUMBER

HH10SS04001



These low profile Filter Fan Shrouds protect filter fan and exhaust grill from wind-driven rain and high-pressure hose water. The shroud does not impede air flow of filter fan and exhaust grille.

INDUSTRY STANDARDS

UL 508A UL/cUL Listed; Type 3R; File No. E482010

Maintains UL/cUL Listed Type 3R and Type 12 rating when properly installed on a Type 3R or Type 12 enclosure

FEATURES

Protects filter fan and exhaust grill from wind-driven rain and high-pressure hose water

Easy one person installation with simple back panel mounting

Easily accessed filter simplifies replacement

PRODUCT ATTRIBUTES

Article Number: 35017

Height: 15in

Width: 12in

Depth: 3.81in

Material: Stainless Steel 304

Finish: Brushed

Thickness: 16ga

Weight: 8.3lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE