

Flat Cover with Latches Type 4X, 15.81x13.81x5.99, Lt Gray, Fiberglass

CATALOG NUMBER

HJ1614HWPL2LG



Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with solid and window covers. Latches provide easy access and security.

INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E54315
cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13;
File No. E54315

Enclosure flammability per UL 508A

NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13

CSA File No. 217184: Type 3, 3R, 4, 4X, 12, 13

IEC 60529, IP66

Meets NEMA Type 3RX requirements Purchase panels separately. Optional stainless steel, composite and aluminum panels are available for most sizes

FEATURES

Compression-molded fiberglass construction

Overlapping solid- and window-cover models are available

Windows are clear polycarbonate

Cover fastens with padlockable Type 316 stainless steel latches

Type 304 stainless steel piano hinges

Integral mounting brackets

Enclosures protect equipment and operators from indirect electrical contact

PRODUCT ATTRIBUTES

Article Number: 15891

Height: 402mm

Width: 351mm

Depth: 152mm

Material: Fiberglass

Finish: Smooth Matte

Color: Light Gray

Color Code: RAL 7035

Thickness: 3.6mm

Latch Quantity: 2

ADDITIONAL PRODUCT DETAILS

A x B x C are internal dimensions.

Purchase panels separately. Optional stainless steel, composite and aluminum panels are available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE