

HR16 Top-Mount Filter Fan, 230V 266 CFM, Black, Steel

CATALOG NUMBER

HR1626413



HR Top-Mount Filter Fans bolt in place to the top of enclosure ensuring a tight seal.

INDUSTRY STANDARDS

UL/cUL Listed; Type 12; File No. E482010

CE

EAC

FEATURES

Enclosure top mounting

Bolt in place to ensure a tight seal

Terminal block connections

Free airflow up to 266 CFM (452 m³ /hr.) or 348 CFM (591 m³ /hr.)

PRODUCT ATTRIBUTES

Article Number: 38512

Airflow: 266ft³/min

Nominal Voltage: 230V

Height: 12.66in

Width: 15.81in

Depth: 4.18in

Max Current: 0.48A

Operating Temperature: 14 – 131°F

Material: Mild Steel

Finish: Powder Coated

Color: Graphite Black

Color Code: RAL 9011

Weight: 2lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE