

LED Light, Indoor/ outdoor

CATALOG NUMBER

LEDHL24VCAN



Hazardous Location LED CAN Light provides efficient indoor or outdoor illumination in hazardous environments. This light is ideal for Class 1, Division 2 hazardous areas. With a robust design, this light has a projected lifespan of 100,000 hours and superior lighting performance with minimal power consumption. This versatile, durable LED light provides mounting flexibility and is easy to install.

INDUSTRY STANDARDS

ETL Listed

Class I Division 2, Groups A, B, C and D, T3

Conforms To CSA.22.2 No. 137, 213, 250 Standards

Conforms To UL 844 & 1598 Standards

Conforms to ISA-12.12-01

Maintains enclosure Type 4, 4X rating when properly installed

FEATURES

Robust construction design for suitable outdoor applications; IP66

Minimum power consumption and superior lighting with 12-24 VDC power input

Maximum lighting with 469 lumens output

360-degree rotation allows flexible and versatile mounting

Wide beam optics with 100-degree angle of illumination

PRODUCT ATTRIBUTES

Article Number: 27164

Material: Stainless Steel 316L

Finish: Brushed

Input Voltage DC: 12 – 24V

Current Rating @ 12 VDC: 0.66A

Current Rating @ 24 VDC: 0.35A

Light Output: 469lm

Weight: 2.3lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE