

# Rear-Access Body for InLine HMI Type 4, fits 250x250mm, Lt Gray, Steel

## CATALOG NUMBER

**LLBR252512**



Rear-Access Body enclosure for InLine HMI has a rear-access door. Open front is configured to install optional fixed bezel or deep-hinged window kit.

## FEATURES

Foam-in-place gasket is furnished

Rear door has a quarter-turn latch with a standard slotted insert which accepts most InLine door accessories

Ground stud is furnished

Drill points on enclosure mark the location for pendant or pedestal mounting

## PRODUCT ATTRIBUTES

Article Number: 49960

Height: 9.84in

Width: 9.84in

Depth: 4.72in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Rear Door Opening: 9.13 x 9.13in

Weight: 5.67lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**