

InLine Landscape Enclosure Window Door Type 4X, 230x770x155mm, Brushed, SS304

CATALOG NUMBER

LWC237716SS



When applications require mounting electrical components the full width of the enclosure, the landscape orientation of this aesthetic InLine Enclosure makes this possible. The full-width mounting brackets can be drilled anywhere along their length, providing maximum mounting flexibility.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File Number E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File Number E61997

NEMA/EEMAC Type 4, 4X, 12

IEC 60529, IP66

FEATURES

Full width bracket for mounting flexibility

Seams continuously welded and ground smooth

External formed body flange trough

Large perimeter body opening

Mounting brackets are spot-welded to top and bottom of enclosure

Mounting brackets have predrilled mounting holes; customer-specific location holes can be drilled for mounting flexibility

Seamless foam-in-place gasket

M6 ground stud with base flange on body; M6 bonding provision with base flange on door

Furnished hardware kit includes panel mounting screws and grounding hardware

Hinged door with removable hinge pins and self-grounding quarter-turn latch system with double seal

Door opens 180 degrees

Window door models include 3/16-in. (4.8-mm) clear polycarbonate window mounted flush with door surface

PRODUCT ATTRIBUTES

Article Number: 11046

Height: 9.06in

Width: 30.31in

Depth: 6.1in

Material: Stainless Steel 304

Finish: Brushed #4

Body Thickness: 14ga

Door Thickness: 16ga

Clear Space Above Panel: 5.51in

Window Size: 28.31in

Mounting Hole Size: 29.19in

Mounting Studs: 28.57in

Cover Style: Window

Weight: 23.7lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE