

nVent-HOFFMAN-Logo-Horizon Photo

We connect and protect

SpectraCool Compact Adv. Corrosion Protection Lvl 1, 800BTU 230V, Brushed, SS316

Catalog Number

N160126G102

SPECTRACOOOL COMPACT INDOOR; N16 AIR CONDITIONER; 34437; N160116G050; 34443; N16

- SpectraCool Air Conditioners are available in three sizes that offer a broad range of cooling capacities and configurations. These units deliver reliable enclosure cooling in demanding environments that features reliable design, clean appearance, easy installation, and a filterless design.
- SpectraCool with Advanced Corrosion Protection Solutions provide industry leading corrosion protection to components critical to the performance of the air conditioner. For applications where air conditioners are exposed to harsh, corrosive, chemical elements. Hoffman utilizes advanced coatings to protect the critical components, extending their life and optimizing the extended performance level of the product.
- Select units come with Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.

Industry Standards

- UL/cUL Listed; Type 12, 3R, 4; 4X optional; File No. SA6453
- CE
- EAC
- IP 56 Internal Loop
- IP 34 on External Loop
- Telcordia GR-487 capable*

Features

- Attractive industrial design with minimal use of visible fasteners
- Level 1 Protection Includes: Protective coatings only applied to copper tubing and coils on the condenser (exterior facing) side as well as thermostat coatings
- Energy-efficient rotary compressor on most models
- Level 2 Protection Include: Everything that was coated in Level 1, plus protective coatings applied to the evaporator (interior facing) side and an additional wrap around the thermostat
- Cleanable, reusable aluminum mesh filter included to protect coils for maximum cooling performance in dirty environments
- R407C, R513A or R134a refrigerants
- 115, 230 and 400/460 VAC 3-phase power input on most models
- Reliable mechanical thermostat on enclosure side of the unit
- All G-series come standard with two separate thermostats for cooling and heating when a heater is equipped
- Operating temperature range from -40 F/-40 C to 131 F/55 C
- Dust-resistant condenser coil allows the unit to be run filterless in most indoor applications
- Dual condenser-side air movers for performance redundancy on G52 and G57 models
- Galvanized or stainless steel cover for rugged factory and outdoor environments
- Exterior and partially recessed mounting options

PRODUCT ATTRIBUTES

- Article Number: 35715

- Nominal Capacity Btu/h: 800Btu/h
- Nominal Capacity Watts: 235W
- Refrigerant: R513A
- Corrosion Resistant: Yes
- Nominal Voltage: 230V
- Number of Phases: 1
- Material: Stainless Steel 316L
- Finish: Brushed #4
- Thickness: 18ga
- Height: 16.51in
- Width: 7.52in
- Depth: 6.3in
- Outdoor Installation: Yes
- Mounting: Side wall
- Operating Temperature: –40 to 131°F
- Max Current: 1.5A
- Ambient Temperature: –40 to 131°F
- Remote Access Control: No
- Weight: 30lb

Additional Product Details

*Partial Recess Mount units are not eligible for Type 4 or 4X ratings. Also not eligible for Telcordia GR-487 certification.

Cutout Adapter options for enclosures with older nVent HOFFMAN or Competitive units for easy transitions to new air conditioners

Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice. This document is system-generated.

nVent.com/HOFFMAN |