

Rack-Mount Sliding Shelf, 19in, 2U, fits 600-800, Black

CATALOG NUMBER

P19SHP68B



The Rack-Mount Sliding Shelf allows easy access to shelf-mounted devices. The shelf is 16-gauge steel with 12-gauge steel supports. The shelf mounts to the front surface of front and back rack angles. When mounted directly to a frame, load rating is 150 lb. (68 kg) with four rack angle mountings and 75 lb. (34 kg) with front rack angle mounting. Rack accessories that are shorter than the enclosure depth can be mounted to rack angles or frame accessory brackets attached to grid straps. Order these items separately.

FEATURES

Shelf is 16-gauge steel with 12-gauge steel supports

Mounts to the front surface of front and back rack angles

Load rating is 150 lb. (68 kg) with four rack angles mounted directly to frame verticals; load rating reduced to 75 lb. (34 kg) with front rack angle mounting only

Rack accessories that are shorter than the enclosure depth can be mounted to rack angles or frame accessory brackets attached to grid straps. Order these items separately

PRODUCT ATTRIBUTES

Article Number: 10013

Material: Mild Steel

Max Depth: 37.4in

Shelf Pullout: 17in

Rack Units: 2U

Weight: 20.3lb

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Thickness: 16ga

ADDITIONAL PRODUCT DETAILS

Note: only mount shelves in applications with four points of attachment.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE