

ProLine G2 Fully Sealed Plinth (100mm Solid Base), fits 800x600mm, Black, Steel

CATALOG NUMBER

P2B186



No need to use a gland plate in the base of the enclosure with the Fully-Sealed Plinth Base (100mm Solid Base), which includes fully-sealed gland plates on the sides. Solid bases can easily be joined, for convenient cable management in joined/ganged enclosures while maintaining Type 12 environmental rating.

FEATURES

Maintains NEMA 12 rating without requiring gland plate

Two side gland plates for cable management options

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Optional Cable Entry Gland Plate for additional cable management solutions

Welded corners

Drill points for locating casters (not included)

Installation hardware included

PRODUCT ATTRIBUTES

Article Number: 30951

Height: 3.94in

Width: 22.2in

Depth: 31.5in

Material: Mild Steel

Weight: 33lb

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Thickness: 14ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE