

# ProLine G2 Gland Plates, fits 1200x400mm, Galvanized

## CATALOG NUMBER

**P2BGP124G**



Gland plates are used with a plinth base to provide cable management solutions while maintaining a NEMA 12 rating. ProLine G2's unique Duro-Stand Gland Plate was designed to bear the weight of a person, making it easier to work on the enclosure when the gland plate is installed.

## FEATURES

Consists of a base mounting surface and adjustable foam gasketed gland plates that permit cable entry

Sturdy, adjustable gland plates designed to bear the weight of a person

Number of plates varies with depth: 400 mm and 500 mm (3 plates); 600 mm (4 plates); 800 mm (6 plates); 1000 mm (8 plates)

Galvanized or painted versions

Sealed to maintain NEMA Type 12 rating

Gland Plates are finished with paint over plated surfaces

Can be used with Plinth Base (100 mm or 200 mm), 100 mm Solid Plinth Base, Mobile Base or Transportation Base

Can be used without a base if casters, levelers or frame feet are installed

Can be rotated 180 degrees for front or rear cable entry

Installation hardware included

Includes additional foam gasketing which can be applied to reposition the gasketed opening towards the center of the cabinet or to create two independent access points

## PRODUCT ATTRIBUTES

Article Number: 30978

Material: Mild Steel

Number of Gland Plate Openings: 3

Weight: 27lb

Finish: Galvanized

Thickness: 14ga

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**