

ProLine G2 Disconnect Plinth Base, 100mm, fits 1200x500mm, Black, Steel

CATALOG NUMBER

P2BP1D125



ProLine G2 Disconnect Components are used with ProLine G2 Disconnect Frames and Doors to configure a custom Disconnect Enclosure Solution for widths >1000 mm wide. These components are identical to the standard ProLine G2 components (i.e. ProLine G2 Solid Tops, Gland Plates, Mounting Subpanel) with the exception that the center support is offset 100mm (to accommodate the hinged mullion).

FEATURES

Solution for disconnect enclosures widths >1000 mm wide

Four access panels for cable management options at the base of the enclosure

Sturdy cast aluminum corner supports for superior performance under load

Corner blocks can be installed onto the base of the frame independent of the cover plates, enabling the cover plates to be attached after integration and just prior to shipment

Stackable up to 400mm in height using Plinth Base Stacking Kit (not included)

100 mm or 200 mm options

To maintain a NEMA Type 12 environmental rating, gland plate must also be used in the base of the enclosure

Installation hardware included

PRODUCT ATTRIBUTES

Article Number: 35057

Material: Mild Steel

Weight: 13.76lb

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Thickness: 16ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE