

ProLine G2 Transportation Base, fits 1200x400mm, Black, Steel

CATALOG NUMBER

P2BT124



ProLine G2 Transportation Bases provide enhanced stability and forklift provisions for modular enclosures up to a maximum of 3000 mm (118.11) total width in a multiple-bay system.

FEATURES

Removable side cover plates allows wire access between bases

Can be used across bayed enclosures up to a maximum of 300mm (118.11in.) total width

Maintains NEMA 12 rating without requiring gland plate

Gasket and installation hardware included

Unique design allows forklift access from each end

Can be configured in a variety of combinations

PRODUCT ATTRIBUTES

Article Number: 31162

Material: Mild Steel

Weight: 85lb

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Thickness: 10ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE