

# ProLine G2 Side Cover, fits 2200x400mm, Painted

## CATALOG NUMBER

**P2CS224**



ProLine G2 Solid Sides enclose the open sides of the modular enclosure frame and have innovative design elements incorporated to ensure fast installation and enhanced structural support.

## FEATURES

Hinge hanger on top for easy alignment

Formed steel hems on the sides of the covers for enhanced structural support and to protect user from sharp edges

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Attach to enclosure frame with low-profile, flat head screws

Door can be reversed without removing the side covers

Used on the sides of the ProLine G2 frame

Not suitable as a barrier between enclosures (instead use the ProLine G2 barrier panel)

Two grounding studs

All mounting hardware included

Side Covers are finished with paint over plated surfaces

## PRODUCT ATTRIBUTES

Article Number: 33654

Height: 85.9in

Width: 14.3in

Depth: 0.79in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Weight: 30lb

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**