

ProLine G2 Disconnect Frames, 2000x1200x600

CATALOG NUMBER

P2FD20126



ProLine G2 Disconnect Frames can be used with ProLine G2 Disconnect Doors and Disconnect components to configure a custom Disconnect Enclosure Solution from standard modular enclosure components.

FEATURES

12-gauge (2.5 mm) roll-formed steel with welded corners, and hybrid frame profile for superior performance under load

Frame features a 25-mm DIN standard, alternating rectangular and round hole pattern

RAL 7035 textured light-gray polyester powder paint finish

Similar in design and construction as other ProLine G2 frames, but incorporates a 100-mm offset due to the presence of a 200-mm mullion door in the disconnect door solution

Includes combination removable center upright/verticals in both the front and rear of the enclosure, again with a 100-mm offset

Disconnect specific frame is required for any enclosure solution >1000mm in width; widths 1000mm or less utilize a standard single-bay frame

PRODUCT ATTRIBUTES

Article Number: 31832

Material: Mild Steel

Max Subpanel Size: 75.0 x 44.4in

Max Rack Mount Unit: 42

Weight: 185lb

Color: Light Gray

Color Code: RAL 7035

Finish: Powder Coated

Thickness: 12ga

ADDITIONAL PRODUCT DETAILS

HxWxD are nominal height, width and depth dimensions.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE