

ProLine G2 Disconnect Mounting Subpanel, 1800x1600, Conductive

CATALOG NUMBER

P2PD1816G



ProLine G2 Disconnect Components are used with ProLine G2 Disconnect Frames and Doors to configure a custom Disconnect Enclosure Solution for widths >1000 mm wide. These components are identical to the standard ProLine G2 components (i.e. ProLine G2 Solid Tops, Gland Plates, Mounting Subpanel) with the exception that the center support is offset 100mm (to accommodate the hinged mullion).

FEATURES

Disconnect specific mounting subpanels are required for frames greater than 1000mm in width; any width 1000mm or less uses a standard mounting subpanel

10 gauge (3.0 mm) mild steel; conductive plated option only

Includes eight sets of EZ-Load Glide Blocks, BV-M6 and Hex Bolts for securing

Similar in construction and function to the standard mounting subpanel, but with 100mm offset mounting holes near the middle of the subpanel, due to the presence of the disconnect mullion door in the enclosure solution

Disconnect mounting subpanel comes standard with Disconnect Package

PRODUCT ATTRIBUTES

Article Number: 32473

Material: Mild Steel

Weight: 250lb

Finish: Galvanized

Thickness: 10ga

ADDITIONAL PRODUCT DETAILS

Frame HxW dimensions are nominal mm.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE