

ProLine G2 Partial Side-Mount Subpanel, 900x400, Conductive

CATALOG NUMBER

P2PPSM94G



The ProLine G2 Partial Subpanel secures to the frame or grid straps and facilitates component mounting without consumption of excess internal space; also available in side-mount configuration.

FEATURES

12 gauge (2.5mm) mild steel; available standard in painted white or conductive finish

Flanges on all four sides for increased rigidity

Partial subpanels can be placed in the rearmost position of the enclosure at any vertical height in 25-mm increments, or placed at any depth using grid straps (not included)

Side-mount partial subpanels can be placed on either side at any vertical height in 25-mm increments

All necessary mounting hardware is included

PRODUCT ATTRIBUTES

Article Number: 33615

Material: Mild Steel

Weight: 14lb

Finish: Galvanized

Thickness: 12ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE