

ProLine G2 Top Mounting Module, Height 300mm, Single-Bay , Flts 800x600, Painted

CATALOG NUMBER

P2TMM386



The Top Mounting Module installs to the top of an enclosure providing space for cable management, and facilitating cable passage into the enclosure from above. The module is constructed from a mini ProLine frame, and as such is joinable to accommodate multi-bay solutions. Removable covers are supplied with the module for sealing purposes, while the standard Solid Top (sold separately or included with Industrial Package) is used to enclose the solution as it is mounted to the top of the module.

INDUSTRY STANDARDS

NEMA Type 12 environmental rating

FEATURES

Solution includes frame, width and depth mounted covers, gaskets for sealing junction between top of frame and module, and all installation hardware to secure to the top of a G2 frame

Solid Top sold separately, but also included with standard Industrial Package

200mm and 300mm heights available

Includes single ground stud per cover

PRODUCT ATTRIBUTES

Article Number: 36402

Frame Type: Single-Bay

Thickness: 16ga

Color: Light Gray

Color Code: RAL 7035

Material: Mild Steel

Weight: 58.53lb

Finish: Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE