

ProLine G2 High-Performance Pagoda Exhaust Vent Cutout Top, fits 800x800mm, Painted

CATALOG NUMBER

P2TPH88

The High-Performance Pagoda Exhaust Vent Cutout Top has a cutout that accepts one high-performance pagoda vent.



FEATURES

Cutout top for High-Performance, Pagoda Exhaust Vents

Bolts are furnished to hold top in position (lifting eyes can be used in place of bolts)

Seamless, polyurethane gasket between top and frame (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Ground studs are included

Note: A High Performance Pagoda Exhaust Vent can be used with any ProLine G2 solid top by requesting a cutout modification

PRODUCT ATTRIBUTES

Article Number: 32717

Material: Mild Steel

Weight: 23lb

Color: Light Gray

Color Code: RAL 7035

Finish: Powder Coated

Thickness: 16ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE